

## **C/S** Cubicle Curtains


## Hospital infections kill more Americans each year than AIDS, car accidents and breast cancer combined.\*



Doctors and nurses may clean hands or wear protective gloves coming into a patient's room, but they are recontaminated with opening or closing a privacy curtain.

Hospital room cleanliness is critical in preventing patients from contracting serious infections yet the changing of cubicle curtains is often overlooked.

A study published in *Infection Control*and Hospital Epidemiology found that
a high percentage of hospital curtains
were contaminated with MRSA, VRE and
C-Diff. Further study found that each of
these organisms was transferred to the
hands of hospital workers. With close
to 18,000 deaths in the United States
alone, it is clear that the cleaning of
cubicle curtains to reduce the risk
of infection is essential. C/S Cubicle
Curtains offers hospitals four easy
ways to help them keep their cubicle
curtains clean.



Enterococci is an antimicrobial resistant bacteria that lives in the intestines.




MRSA is a staph infection caused by S. aureus that lives on the skin or in the nasal passage.



The Clostridium difficile bacterium generally acquired in hospitals causes inflammation of the colon.


There is a solution: Changing the curtains between each patient.


C/S gives you four ways to do that quickly, easily and economically.












Getting the best privacy curtains has never been easier or faster—now you can buy online


Hospitals and contractors can now purchase C/S Cubicle Curtain products online. Included are: track systems and track options, I.V. pendants, standard curtain fabrics and disposable curtains. Go to www.c-sgroup.com/curtainstracksystems

## Introducing Qwik Track The quiet, hookless curtain/track system that allows you to remove curtains for cleaning in less than a minute. **FEATURES:** • Curtain rings are integrated in the curtain fabric and are designed to mount directly on the track. • A quiet track for new construction or adaptors to use with existing track systems. Rugged curtain rings can withstand **Qwik Track patented hookless** rings are the key to the system. countless washings. Qwik Track's patented Hookless curtain • Change curtains fast by manually placing them rings are key to the hookless curtain on track or with our special installation tool concept. There are no more hooks, chains, snags and noise, and they allow you to (see page 5). remove or install your curtain in seconds. • Hookless curtain rings can be used on any fabric.

## Qwik Track gives you two ways to change curtains—fast!









With our exclusive curtain wand, your staff can remove or install curtains in seconds without the use of ladders. Simply insert the wand in the hookless rings and push onto the quiet glide track.

## Qwik Track can be used with existing track systems.

With our special track adaptors we can adapt your existing track with Qwik Track's silent guide rails, saving you the cost of buying a new track system.



## C/S Cubicle Curtains Standard Track System Cubicle Track Products

Cubicle Curtains offer a track system

Since the early 1960s, C/S Cubicle Track Systems

have been the industry standard for high quality privacy curtain track systems. Manufactured from high quality aluminum extrusions, C/S track systems

including Qwik Switch (page 9) provide smooth,

calls for surface mounting, straight or radiused run,


snag-free operation. Whether your application

C/S Cubicle Tracks are designed to stay put, no

matter how hard the curtain is pulled.

for every type of room and

ceiling condition.







Our snag-free, dual channel extruded aluminum track is 1-3/8" wide x 3/4" deep.
Specify anodized aluminum or white baked enamel.



Surface Mounted I.V. Track

This track is manufactured exclusively for I.V. Pendants. Specify anodized aluminum or white baked enamel.



Narrowline Surface Mounted Track

Our new Narrowline anodized aluminum track is 29/32" wide x 11/16" deep. It also provides smooth, snag-free operation.



#### Suspended Mount Aluminum Track

This track system includes 3/4" square aluminum hangers with suspension brackets made of molded nylon (white or aluminum color). Suspended tracks are generally set 7'3" from finished floor.



Carrier Gate

The carrier gate assembly is used at all curtain stacking points. Assembled with a machine screw, the carrier gate provides easy insertion or removal of carrier.



## 'T' Bar Mounting Clip

This clip allows our standard track system to mount to a 'T' grid ceiling without the use of screws. Available for traditional grid ceilings and regular tile installations.



Splice

These 6" track splices are used where one-piece sections are not long enough or where radius and straight track connects. Available in white or anodized satin aluminum.



### **Carrier Stop**

The carrier stop is used at the ends of curtain tracks or bends. Made of molded nylon, our stops are finished to match track color.



18/20 Offsets

Used to wrap track around the foot of the bed, the 30°-45° bends are supplied 2'x2' or in custom lengths. Available in white or anodized aluminum.




#### **Wall Socket**

This component is designed to secure suspended mounted track systems to the wall. Available in white or anodized aluminum.



## C/S Cubicle Curtains Cubicle Track Options and I.V. Pendants





General Carrier 1062N

Combines a nylon axle and a wheel with a nickel plated brass bead chain and polished aluminum hook.



General Carrier 975
A super smooth economical carrier manufactured completely from nylon including nylon axle wheels.



Spool Carrier SP062

Designed for use in any C-Channel curtain track. Manufactured from Nylon/Delrin, these carriers provide fast, free movement.



Breakaway Carrier 975P

For use in psychiatric institutions. The hook is designed to pop out of the axle when 22 lbs of pressure is applied.



Self-Locking I.V. Carriage
For use with I.V. Track 17000 (straight track only). Carrier is equipped with steel alloy wheels that ride inside the track.



Twist Lock I.V. Carriage

Made of Celcon this locking I.V.
carriage's shaft and hook are nickel
chrome plated steel.



Deluxe 8 Bottle I.V. Pendant
Stainless model 17800 telescopes from 28" to 42". Two sets of folding arms hold 8 total bottles.



Deluxe 5 Bottle I.V. Pendant
3/4" Stainless model 17150 telescopes from
28" to 42". Four folding safety arms and a
fifth hook at the base.



9/16" Stainless model 17100 telescoping I.V. 19" to 32" for low ceiling applications, includes four folding arms.

## **Introducing Qwik Switch**°

The easy way to change privacy curtains from the ground using our standard track system

**BUY ONLINE** 

**Step 1** Insert the Qwik Switch wand into the locking unit at the end of the track where the ceiling meets the wall. Turn the wand counterclockwise to unlock the latch and bring the track down to remove the curtain.



**Step 2** Load a clean curtain onto the carrier. Using the Qwik Switch wand, push the track back up to the ceiling, and the Qwik Switch locking unit will lock the track back into position.



# Use in new construction or we can adapt your existing curtain track.




**Qwik Switch Hinge**The Qwik Switch hinge allo

The Qwik Switch hinge allows the track system to pivot down for removing curtains from their carriers. Hinged sections of track are available in lengths up to 6' in a finish to match clear anodize.



**Qwik Switch Latch** 

The Qwik Switch Locking Units, attached to the track end, lock onto the Qwik Switch Latch, which is hard fastened directly to the ceiling. Available in finish to match clear anodize.



**Qwik Switch Wand** 

With a simple turn of the 48" wand, workers can bring the privacy curtain down for laundering and easily put up clean fresh curtains while standing on the ground.

## **C/S** Cubicle Curtains

# We manufacture the finest privacy curtains available anywhere.



## Quality makes the difference.

All C/S Cubicle Curtains are manufactured using double needle interlock tailoring.
This process ensures durability, and the curtains will have a finished look on both sides where the nylon mesh meets the curtain.

The attention to details on every C/S curtain is evident, whether you specify one of our standard fabrics (page 14-19) or a custom designer fabric from any textile house. All of our privacy curtains feature double needle interlock stitching for durability and a finished look. Additionally, all edges of our nylon mesh are completely bound with the same fabric as the body of the curtain, and the grommets at the top of the curtain are firmly anchored to triple thick hems for long life. C/S also offers a complete line of colorcoordinated nylon mesh to minimize its appearance at the top of each curtain. And all of our curtains meet the flame resistant regulation NFPA requires for the use of privacy curtains in health facilities.

## One look says it all!





#### **Custom Fabrics**

We consistently deal with the world's finest textile companies, including Maharam, Architex, Design Tex, Interspec, Design/Craft and Carnegie. Whichever custom fabric you select for your project, C/S can supply it effortlessly to your exact specifications. Call 800-869-4606 for details.

## maharam

Carnegie

Architex®

Design Tex





1



Snap Lock

A modular curtain system that allows you to remove the fabric portion of the curtain for regular washings.



Because of their modular design Snap Lock Curtains can be used in any patient room or other area requiring privacy curtains.


c/S' Snap Lock Curtain System is designed to help facilities easily and effectively deal with the cleaning of privacy curtains. This curtain system eliminates the hassles and dangers of removing cubicle curtains from ceiling mounted track systems. Instead of getting on a ladder to remove the privacy curtain, Snap Lock allows the hospitals' maintenance staff to separate the fabric portion of the curtain from the mesh while standing on the ground. Soiled curtains are then laundered, and the maintenance staff snaps clean curtains back onto the mesh. And Snap Lock curtains are designed to be modular, so a facility can buy dozens of the same curtain in a specific size and use them interchangeably from room to room. This affords the hospital an easy way to manage its curtains and to always have spares on hand. And modular curtains can save facilities money, by not having to purchase a lot of custom or different size curtains.

# Introducing C/S Disposable Curtains

## Ideal for highly contagious areas



C/S Disposable Curtains are perfect for critical care, isolations and emergency areas in healthcare facilities. C/S Disposable Curtains look just like fabric curtains and are cost effective when compared with the life-cycle cost of traditional fabric curtains. Isolation curtains can be hung on any of our track systems or any standard curtain track. C/S Isolation Curtains are manufactured from 100% recyclable material, they are 99% biodegradable and they meet NFPA 701 standards and are extremely strong. An antimicrobial finish is standard on all curtains. Our isolation curtains are available with and without mesh, and both types come in a protective hygienic sleeve.



12

## Acrovyn°

## maharam

Acrovyn, the leader in wall protection, and Maharam, one of the top designer fabric companies, have created a color-coordinated palette so your hospital's walls and cubicle curtains can coordinate beautifully.



### **○** For comprehensive information on these products, visit www.c-sgroup.com

## C/S Cubicle Curtains Standard Fabric Selector

## Allegro (Antimicrobial)




### **Connections** (Antimicrobial)



15

14

## C/S Cubicle Curtains Standard Fabric Selector





#### Windsor



### **New Shadow Cube** (Antimicrobial)



#### Fantasia

Blue Moon



## C/S Cubicle Curtains Standard Fabric Selector





#### **General Cubicle Oxford**



### Hastings



#### Petals



### **Sure-Chek Linen Shower Curtains**



## **New Shower Shield Shower Curtains** (100% Polyester and Antimicrobial)



 $<sup>\</sup>begin{tabular}{ll} \hline \end{tabular} For comprehensive information on these products, visit www.c-sgroup.com \\ \hline \end{tabular}$ 

<sup>\*</sup> Standard 48 hour quick ship colors and Antimicrobial.



49 Meeker Avenue, Cranford, New Jersey 07016 U.S.A., 908-272-5200 895 Lakefront Promenade, Mississauga, Ontario L5E 2C2 Canada, 905-274-3611

• www.c-sgroup.com



For more than 60 years, Construction Specialties has been a leader in architectural specialty products, including: Acrovyn<sup>a</sup> Wall and Door Protection, Pedisystems<sup>a</sup> Entrance Flooring, Expansion Joint Covers, Cubicle Track and Curtains, Smoke and Explosion Venting Systems, Architectural Grilles, Architectural Louvers and Sun Controls.

We have operations throughout the world and can provide C/S Products virtually anywhere. For a complete list of our international locations, visit www.c-sgroup.com.



For the nearest C/S representative, or literature and samples, call toll free 800-631-7379 in U.S.A. and 888-895-8955 in Canada, or visit www.c-sgroup.com

